



ABC Charger 1230

12 V built-in charger for professional use with adjustable charging characteristic for gentle charging of the battery.

- // For all types of lead batteries
- // Also available in protection class II
- // 15 selectable charging characteristics
- // Complies with DIN 14679:2024-02

The ABC 1230 charger: Optimal charging of 12 V batteries with a charging current of 30 A. In addition, a remote display or a temperature sensor (CTS) can be connected. The battery charging is fully automatic and microprocessor-monitored with selectable charging characteristic - thus an optimal and gentle charging is guaranteed.

Technical Information

| | |
|-------------------------------------|-----------------------------------|
| CBL connection | No* |
| Charging current | 30 A* |
| Connector, AC input | Schuko plug (type F)* |
| Connector Temperature Sensor | Yes* |
| Output voltage (DC) | 12 V* |
| Power category | 600 W - 800 W* |
| Protection class | I* |
| Remote display connection | Yes* |
| Battery capacity | 90 Ah ... 300 Ah |
| Building main fuse | B16 A/C16 A |
| Cable length, AC input | 1.5 m, 0.75 mm ² |
| Cable length, DC output | 2 x 2 m, 6 mm ² |
| Charging characteristic | 15 selectable charging programmes |
| Complies with DIN 14679:2024-02 | yes |
| Input frequency range | 47 Hz ... 400 Hz |
| Input voltage (AC) | 230 V |
| Input voltage range | 90 V ... 270 V |
| International Protection (IP class) | IP21 |
| Level of efficiency | > 88 % |
| Main charge | 14.2 V/14.4 V |
| On/Off switch | Yes |
| Operating temperature | -30 °C ... +60 °C |
| Ripple | < 3 % |
| Switching frequency | 100 kHz |
| Dimensions (L x W x H) | 220 x 112 x 73 mm |
| Weight | 1.5 kg |

*In the chosen option

Product information sheet

Product number: 0101036130

Date: 24.11.2024

Page: 3/3



Technical Information

| | |
|-----------------------|---------------|
| Trickle charge | 13.6 V/13.8 V |
|-----------------------|---------------|

| | |
|------------------------|---------------------------|
| Type of battery | Lead acid (wet, gel, AGM) |
|------------------------|---------------------------|

*In the chosen option